

INSTALLING Guide Flexi-Fit HANDRAIL

- 1. Remove insert from the rail by freeing one end of the PVC and pulling back along the rail length. It simply peels out.
- 2. Once the substrate fixing points have been established, slide the the nut inside the channel. Then tighten the locking nut with a Fasten by revolving the W75 bracket or screwing the W60 into brackets along the rail length until they are at the required posit '8" open ended spanner, ensuring the bracket is at right angles
- With a sharp cutting tool, cut the PVC into lengths to fit into the ends of rail. cavities between the brackets, and between the brackets and
- 4. Push the PVC into place by pressing down on it. This process minutes. is easier after the PVC has been immersed in hot water for three
- 5. Pre-drill the fixing holes with a 3.5mm drill bit.
- 6. Screw the assembled rail into place at a height of between 900mm and one metre with a size 2 square drive bit or
- Any dirty marks on the rail or insert resulting from installation can usually be removed with a Jif-like product and a wet cloth

Guide The rail with adjustable brackets



HOW TO PURCHASE & INSTALL YOUR Guide Flexi-Fit HANDRAIL



GUIDE AROUND THE HOME (HANDRAILS)

Guide is a well-known and respected system of premium quality aluminium handrails which is used throughout New Zealand and in

to the most suitable substrate (fixing points). which provide the flexibility required to ensure that brackets are fixed Guide Flexi-Fit features unique, patented sliding brackets

of maintenance free enjoyment. Guide Flexi-Fit has an attractive and durable finish for years

can be used for both interior and exterior applications. And because the brackets and rail won't rust, Guide Flexi-Fit



complete with the components required for assembly and Guide Flexi-Fit handrails are supplied as 45mm diameter rail, installation.

handrail display stand but can be ordered in if required. Note: Guide Flexi-Fit 32mm handrail is not supplied on the

GUIDE IN THE BATHROOM (SAFETY GRAB RAILS)

Guide Flexi-Fit safety grab rails are supplied in a range of sizes degree rails. Standard colours include white, bright silver and almond. from 450mm straight lengths through to 750mm x 750 mm ninety

bathroom department in-store, or ask the helpful staff. diameter finished product. Look for the distinctive packaging in the Guide Flexi-Fit safety grab rails are supplied as a 32mm



PURCHASING Guide Flexi-Fit HANDRAIL

three metres. Lengths up to five metres are available on reques: Guide Flexi-Fit handrail is supplied in lengths of one, two and **Length -** The first thing to decide is the length of rail required

commonly used with black rail, silver supplied in three standard colours - black, brackets for silver rail and off white for off silver and off white. Black brackets are most Colour - Guide Flexi-Fit handrail is



handrail stand you will find two different types of brackets. Brackets - On the Guide Flexi-Fit white rail.

a wall. The W75 bracket is used for mounting Guide Flexi-Fit handrail on the side of



metres of rail, three brackets for two metres For secure fixing, allow four brackets for three (such as an interior halfwall).

Guide Flexi-Fit handrail on top of a wall

The W60 bracket is used for mounting

of rail and two brackets for one metre of rail.

concrete, masonry or steel, ask for guidance from staff in-store. or dwang, no additional screws are required. When fixing into brick, screwdriver) are supplied with each bracket. For fixing into timber stud Fixings - Square drive screws (which require a size 2 drive bit or

rail - black insert with black and silver rail, and white with off white rail. **PVC Insert - PVC insert is prepackaged with each length of** as pairs. Black end caps are most commonly used with black and silver rail, while white is more common for off white rail.

End Caps - End caps are available in black and white, packaged

Purchase checklist

Brackets - right kind (W75 / W60) Rail of required length and colour

Brackets - preferred colour Brackets - right number

End caps- preferred colour