

# HEALTHCARE SPECIFIERS CATALOGUE



## ARCHITECTS CHOICE



### Recently installed at:



Wellington Children Hospital



North Shore Hospital -Totara Haumaru



Palmerston North Hospital



**Canterbury Charity Hospital** 

### HEALTHCARE TRACK




We offer two types of healthcare tracks:





Example of track layout:



or

### Track accessories:



Offering custom made designs that can solve multiple bends and sloping ceilings + walls

### ANTIMICROBIAL CURTAINS



Mactrac Care offers two options within the Antimicrobial Curtain range:



Hospital Curtains
Mesh top



Clinical Curtains
Standard top

### Colours available:

- Block dark blue
- Block Cream
- · Sea blue with design



Mactrac Care Antimicrobial Curtains have been tested for:

- Antimicrobial Properties with ISO 20743
- Antimicrobial Prosperities with AATCC 100
- Fire retardancy to NZ & AU standard AS 1530.2.
   Flammability Index = 1

### Code, size & colour:

| Tetral Code | Product Description                                | Size      | Colour      | Product detail         |
|-------------|--|-----------|-------------|------------------------|
| M26CR375    | DISPOSABLE CURTAIN BLOCK CREAM 3.75 X 2.0M         | 3.75x2M   | Block Cream | Antimicrobial Curtains |
| M26CR750    | DISPOSABLE CURTAIN BLOCK CREAM 7.5 X 2.0M          | 7.5x2M    | Block Cream | Antimicrobial Curtains |
| M26DB375    | DISPOSABLE CURTAIN BLOCK DARK BLUE 3.75 X 2.0M     | 3.75x2M   | Block Blue  | Antimicrobial Curtains |
| M26DB750    | DISPOSABLE CURTAIN BLOCK DARK BLUE 7.5 X 2.0M      | 7.5x2M    | Block Blue  | Antimicrobial Curtains |
| M26SB375    | DISPOSABLE CURTAIN SEA LIGHT BLUE 3.75 X 2.0M      | 3.75x2M   | Sea Blue    | Antimicrobial Curtains |
| M26SB750    | DISPOSABLE CURTAIN SEA LIGHT BLUE 7.5 X 2.0M       | 7.5x2M    | Sea Blue    | Antimicrobial Curtains |
| M27SB550M   | DISPOSABLE CURTAIN SEA LIGHT BLUE MESH 5.5 X 2.35M | 5.5x2.35M | Sea Blue    | Antimicrobial Curtains |
| M27SB750M   | DISPOSABLE CURTAIN SEA LIGHT BLUE MESH 7.5 X 2.35M | 7.5X2.35M | Sea Blue    | Antimicrobial Curtains |



| Code       | Name                                  | Image | Detail  | Can be used on                                | # Screws<br>required | # Rivets required |
|------------|---------------------------------------|-------|---|---|----------------------|-------------------|
| M40FAS06   | S/steel screw 8G<br>x 1 1/4           | *     | Track fixing screw  | For fixing THF to ceiling & AWB to wall       | ·                    |                   |
| M40FAS08   | Rivets for<br>bathsets silver 5-<br>3 |       | Track rivet silver  | For attaching<br>fittings to h/rod &<br>track |                      |                   |
| M40CTCAWB_ | AWB/2                                 |       | Wall bracket for<br>Pro/SC2   | Mactrac Pro/SC2                               | 2                    | 1                 |
| M40CTCECB_ | ECB/2                                 |       | End cap bracket<br>Pro/SC2  | Mactrac Pro/SC2                               |                      | 1                 |
| M40CTCBHF_ | ВНҒ                                   |       | Bottom hanger ferrule<br>attaches hanger to<br>track  | Mactrac Pro/SC2                               |                      | 3                 |
| M40CTCTHF_ | THF                                   |       | Top hanger furrule<br>attaches hanger to<br>track   | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3    | 2                    | 1                 |
| M40CTCSCB_ | Sloping Ceiling<br>Bracket            |       | Use SCB when the ceiling isn't horizontal   | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3    | 2                    | 2                 |
| M40CTCCFB_ | Ceiling Fixing Brkt<br>L-shaped       |       | For mounting tracks direct to ceiling   | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3    | 1                    | 1                 |
| M40CTCJ2_  | Junction Plate<br>SC2                 |       | Join 2 tracks at a bend<br>junction for<br>suspended only LH &<br>RH options, add<br>240mm to straight<br>track | Mactrac Pro/SC2                               |                      | 4                 |
| M40CTCSB2_ | Swivel Bracket<br>SC2                 |       | to join track to wall if<br>not at 90 degree angle  | Mactrac Pro/SC2                               | 2                    | 2                 |



| Code       | Name                             | Image | Detail   | Can be used on                             | # Screws<br>required |   |
|------------|----------------------------------|-------|--|--|----------------------|---|
| М20ВН06_   | 0-600MM Hanger<br>rod            | A A 4 | 600mm ceiling support with 1 x BHF, 1 x THF, 2 x screws & 3 x rivets                           | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3 |                      |   |
| M40CTCHT_C | Hanger Tube Cut<br>per m         |       | Hanger rod cut to order<br>available in lengths up to<br>1800mm                                | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3 |                      |   |
| M40CTCTJP_ | Tee Plate SC2 or<br>SC3 P/coated |       | For join straight tracks at 90 degree intersection (no bend) 3 way & 4 way options             | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3 |                      | 4 |
| М40СТСТЈС  | Metal Joiner SC2<br>220mm        |       | standard internal joiner   | Mactrac Pro/SC2                            |                      | 4 |
| M40CTCP2_C | P2 BRACKET FOR<br>SC2 COMPLETE   | D)    | 50mm bracket for fixing tracking parallel to the wall on at end of track 2 x screws, 1 x rivet | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3 |                      |   |
| M40CTCAFP_ | AFP Ceiling Ferrule<br>SC2/SC3   |       | rod bracket for false<br>ceiling   | Mactrac Pro/SC2<br>Mactrac Pro<br>Plus/SC3 |                      | 1 |
| М50МВ      | BEND                             |       | 300mm radius bend,<br>custom can be done   | Mactrac Pro/SC2                            |                      |   |



| Code       | Name                            | Image | Detail  | Can be used on                          | Finishes |
|------------|---------------------------------|-------|---|---|----------|
| M40GLNRS1  | NRS1<br>Stainless<br>Steel Hook |       | Nylon ring glide with stainless steel hook              | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 |          |
| M40GLNRS2  | NRS2 Ring<br>Glide              |       | INVION TING GUIDE                                       | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 | white    |
| M40GLNRS9  | NRS9 Plastic<br>Hook            | 7 2   | Nylon ring glide with acetyl hook                       | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 | white    |
| M40GLNG4   | NG4                             | Δ     | 1 ' ' '   | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 | white    |
| M40GLNG4S  | NG4 Glide<br>with SS hook       |       | MIND WITH CTAINIACC                                     | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 |          |
| M26QCLIP   | QUICK CLIP                      |       | Easy attachment for<br>Antimicrobial<br>curtain to NRS2 | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 | white    |
| M40CTCFUSE | ANTI-<br>LIGATURE<br>FUSE       |       | inrovidos a solution                                    | Mactrac Pro/SC2<br>Mactrac Pro Plus/SC3 | n/a      |



| Codo       | Nome                              | I     | Datail   | Can be                        | # Screws | # Rivets |
|------------|-----------------------------------|-------|--|-------------------------------|----------|----------|
| Code       | Name                              | Image | Detail   | used on                       | required | required |
| M40CTCAW3_ | AWB/3                             |       | Wall bracket   | Mactrac<br>Pro<br>Plus/SC3    | 2        | 1        |
| M40CTCEC3_ | ECB/3                             | 0     | End cap bracket<br>for SC3                             | Mactrac<br>Pro<br>Plus/SC3    |          | 1        |
| M40CTCSB3_ | Swivel Bracket SC3                |       | For track to join<br>wall not at 90<br>degrees         | Mactrac<br>Pro<br>Plus/SC3    | 2        | 2        |
| М40СТСВН3_ | BHF/3                             |       | Bottom hanger<br>ferrule rod to<br>track bracket       | Mactrac<br>Pro<br>Plus/SC3    |          | 3        |
| M40CTCJ3   | Junction Plate SC3                |       | For bend<br>junctions on<br>suspended track<br>LH & RH | Mactrac<br>Pro<br>Plus/SC3    |          | 6        |
| М40СТСТЈЗ  | Joiner SC3                        |       | standard internal joiner for tracks                    | Mactrac<br>Pro<br>Plus/SC3    |          | 4        |
| M40FAS22   | SC3 5-6 Rivet white               |       | For attaching brackets to track & tube                 | Mactrac<br>Pro<br>Plus/SC3    |          |          |
| M40CTCCFP_ | Ceiling fixing plate -<br>Round   |       | For ceiling fixed IV or Stage track                    | Mactrac<br>Pro<br>Plus/SC3 IV | 2        | 4        |
| M40CTCIVJP | IV TRACK JOINING PIN              |       | Internal joiner for<br>SC3 IV tracks                   | Mactrac<br>Pro<br>Plus/SC3 IV |          |          |
| M40CTCIVGL | IV GLIDER COMP WITH<br>S/STEEL HK | j     | Glide & hook for<br>IV track                           | Mactrac<br>Pro<br>Plus/SC3 IV |          |          |



| Code        | Name                                     | Image | Detail   | Can be used on                       | # Screws required | # Rivets required |
|-------------|--|-------|--|--------------------------------------|-------------------|-------------------|
| M40CTCMVTS  | Move Track Pivoting T-<br>Slider         |       | Pivoting T Slider<br>for Gantry track                  | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY | ·                 | ·                 |
| M40CTCIVGLD | Double Slider for Large<br>Spans over 3m | 0     | Double slider<br>support for large<br>spans            | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY |                   |                   |
| M40CTCEC3L_ | ECB for Gantry Track<br>LH               | 4     | End cap for<br>Gantry track<br>against wall            | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY |                   | 1                 |
| M40CTCEC3R_ | ECB for Gantry Track<br>RH               |       | End cap Gantry<br>track against wall                   | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY |                   | 1                 |
| M40CTCMVIEB | Internal Stop for<br>Gantry Track        |       | 20mm Internal<br>end stop for<br>Gantry track          | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY |                   |                   |
| M40CTCMVJ   | Joiner SC3/Gantry<br>Track               |       | Joining SC3 to<br>Gantry tracks or<br>Gantry to Gantry | Mactrac<br>Pro<br>Plus/SC3<br>GANTRY |                   |                   |